



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR250ST Type BR BRKR 50A/2 Pole 120/240V 10K W/Shunt Trip

Eaton Corp

Catalog Number	BR250ST
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Shunt Trip Circuit Breaker, 50 A, 10 Kaic, Two-Pole, 120/240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters, Shunt Trip Included
Weight per unit	0.9400 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

dimensions	4.2500 IN X 4.0000 IN X 3.5000 IN
interrupt rating	10 kAIC
Poles	2
Trip Type	Common breaker trip
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR BRKR 50A/2 POLE 120/240V 10K W/SHUNT TRIP
extra long description	ETN BR250ST BR 50A/2 Pole 120/240V
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on shunt trip circuit breaker, 50 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters, Shunt trip included
Product Type	BR 50A/2 Pole 120/240V 10K W/Shunt Trip
Special Features	Shunt Trip

Manufacturer Information

Brand	Eaton
GTIN	00786676000345
Manufacturers Part Number	BR250ST
UPC	786676000345

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Package	10
Weight Per each	0.94

Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper Converged Other Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Generation - Conventional Energy - Conventional Energy
standard	UL 489, Federal Specifications Classification W-C375