



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR315 Type BR BRKR 15A/3 Pole 240V 10K *Eaton Corp*

Catalog Number	BR315
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 15 A, 10 Kaic, Three-Pole, 240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	1.3 (lbs/each)
Product Category	3 Pole Standard Trip Plug-In

### Features

amps	15
dimensions	2.9000 IN X 2.9000 IN X 2.6000 IN
interrupt rating	10 kAIC
pole #	Three
Poles	3
Trip Type	Common breaker trip
Voltage Rating	240 V - 240 V

### Descriptions

Description	TYPE BR BRKR 15A/3 POLE 240V 10K
extra long description	ETN BR315 Type BR Breaker 15A/3 Pol
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 15 A, 10 kAIC, Three-pole, 240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	Type BR Breaker 15A/3 Pole 240V 10K

### Manufacturer Information

Brand	Eaton
GTIN	00786676367707
Manufacturers Part Number	BR315
UPC	786676367707

### Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	5
Weight Per each	1.25

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherDatacenters - IT Space: CI and Hyper ConvergedGeneration - Conventional Energy - Conventional Energy
standard	UL 489,Federal Specifications Classification W-C375