



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BPC8 SPRG 1/2" 2PC, 200LB CNDT Clamp

Cooper B-Line/Cable Tray

Catalog Number	BPC8
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Conduit Support Fasteners, Conduit and Cable, 1" Height, 1" Length, 1" Width, 0.091LBS, Rigid or Emt Conduit Size: 0.5", Break-Apart Conduit Clamps, 200 LBS Load Capacity, Pre-Galvanized
Weight per unit	0.0009 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
Material	Plastic

Material, Color, and Finish

Color	Black
Finish	N/A

Dimensions and Weight

Size	1-1/2 In (Pipe), 1-5/8 In (Tubing)
------	------------------------------------

Descriptions

Also Known As...	Strut Strap Strut Clamp Pipe Clamp for Strut Conduit/Pipe Clamp for Strut
Construction	ONE PIECE
Description	SPRG 1/2" 2PC, 200LB CNDT CLAMP
extra long description	B-LINE BPC-8 BREAK-APART CLAMP, 1/2
Features	Designed for ease of installation, long service life and reliable performance, Eaton B-Line series conduit support fasteners provide the ideal choice for a wide range of applications.
Long Description	Eaton B-Line series conduit support fasteners, Conduit and cable, 1" Height, 1" Length, 1" Width, 0.091lbs, Rigid or EMT conduit size: 0.5", Break-apart conduit clamps, 200 lbs load capacity, Pre-galvanized
Product Type	Break-Apart Clamp, 1/2" Rigid or Emt
Special Features	Weight 4 Lb per 100



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00781011016760
Manufacturers Part Number	BPC8
UPC	781011016760

Taxonomies, Classifications, and Categories

Category Description	STRUT STRAPS
Type	Break apart conduit clamp

Packaging

Carton	1
Package	100
Weight Per each	0.0009

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket
Mounting standard	CHANNEL UL/cUL Listed
Temperature Rating	-40 To 275 Deg F