

# Specifications

## Eaton BR60120B200R

Main circuit breaker  
loadcenter,200A,Aluminum,NEMA 3R,120  
circuits,60 spaces,Single-  
phase,Top/bottom,120/240V



### General specifications

<b>PRODUCT NAME</b>	Eaton BR main breaker loadcenter
<b>CATALOG NUMBER</b>	BR60120B200R
<b>UPC</b>	786685931708
<b>PRODUCT LENGTH/DEPTH</b>	5.2 in
<b>PRODUCT HEIGHT</b>	48.75 in
<b>PRODUCT WIDTH</b>	14.3 in
<b>PRODUCT WEIGHT</b>	50 lb
<b>WARRANTY</b>	10 year
<b>COMPLIANCES</b>	UL67
<b>CERTIFICATIONS</b>	UL Listed file E52977



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Main circuit breaker loadcenter
<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	120
<b>NUMBER OF SPACES</b>	60
<b>PHASE</b>	Single-phase
<b>FEED TYPE</b>	Top/bottom
<b>VOLTAGE RATING</b>	120/240 V
<b>ENCLOSURE</b>	NEMA 3R

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BR60120B200R</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton BR60120B200R

Main circuit breaker  
loadcenter,200A,Aluminum,NEMA 3R,120  
circuits,60 spaces,Single-  
phase,Top/bottom,120/240V



### General specifications

<b>PRODUCT NAME</b>	Eaton BR main breaker loadcenter
<b>CATALOG NUMBER</b>	BR60120B200R
<b>UPC</b>	786685931708
<b>PRODUCT LENGTH/DEPTH</b>	5.2 in
<b>PRODUCT HEIGHT</b>	48.75 in
<b>PRODUCT WIDTH</b>	14.3 in
<b>PRODUCT WEIGHT</b>	50 lb
<b>WARRANTY</b>	10 year
<b>COMPLIANCES</b>	UL67
<b>CERTIFICATIONS</b>	UL Listed file E52977



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Main circuit breaker loadcenter
<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	120
<b>NUMBER OF SPACES</b>	60
<b>PHASE</b>	Single-phase
<b>FEED TYPE</b>	Top/bottom
<b>VOLTAGE RATING</b>	120/240 V
<b>ENCLOSURE</b>	NEMA 3R

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BR60120B200R</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

