



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR816N200RF

UPC:786676448451

Dimensions:

- **Height:** 25 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

Notes:The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Warranties:

- 10 year

Specifications:

- **Special Features:** Feed-through lug
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** C3r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 16
- **Number Of Spaces:** 8
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Voltage Rating:** 120/240V
- **Wire Size:** Determined by circuit breaker installed

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light](#)



Commercial

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR816N200RF](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR816N200RF

UPC:786676448451

Dimensions:

- **Height:** 25 IN
- **Length:** 5.19 IN
- **Width:** 14.31 IN

Notes:The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Warranties:

- 10 year

Specifications:

- **Special Features:** Feed-through lug
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** C3r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 16
- **Number Of Spaces:** 8
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Voltage Rating:** 120/240V
- **Wire Size:** Determined by circuit breaker installed

Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light](#)



Commercial

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR816N200RF](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data