



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BQ250250 BQ Quad BRKR 2 -50A/2P Indep. Trip 120/240V 10K

Eaton Corp

Catalog Number	BQ250250
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BQ 1-Inch CTL Plug-On Circuit Breaker, Includes Rejection Tab Feature, (2) Two-Pole 50 A, 10 Kaic, Four-Pole, 120/240V, BQ, Independent, #14-4 Awg Cu/Al, Q28, BQ, Type BR Loadcenters
Weight per unit	0.9000 (lbs/each)
Product Category	Quadplex Standard Trip Plug-In

Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	Four-pole
Trip Type	Independent
Voltage Rating	120/240 V

Descriptions

Description	BQ QUAD BRKR 2 -50A/2P INDEP. TRIP 120/240V 10K
extra long description	ETN BQ250250 BQ Quad 2 -50A/2P 120/
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BQ 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Two-Pole 50 A, 10 kAIC, Four-pole, 120/240V, BQ, Independent, #14-4 AWG Cu/Al, Q28, BQ, Type BR Loadcenters
Product Type	BQ Quad 2 -50A/2P 120/240V 10K
Special Features	Includes Rejection Tab feature

Manufacturer Information

Brand	Eaton
GTIN	00786676371254
Manufacturers Part Number	BQ250250
UPC	786676371254

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.9

Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL 489, Federal Specifications Classification W-C375