



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BQC230240 BQC Quad BRKR 1-30A/2P 1-40A/2P Com. Trip 120/240V *Eaton Corp*

| | |
|------------------|--|
| Catalog Number | BQC230240 |
| Manufacturer | Eaton Corp |
| Description | Eaton BR Thermal Magnetic Circuit Breaker, Type BQC 1-Inch CTL Plug-On Circuit Breaker, Includes Rejection Tab Feature, (1) Two-Pole 30 A, (1) Two-Pole 40 A, 10 Kaic, Four-Pole, 120/240V, BQC, Common Breaker Trip, #14-4 Awg Cu/Al, BQC |
| Weight per unit | 0.9000 (lbs/each) |
| Product Category | Quadplex Standard Trip Plug-In |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 3.0000 IN X 2.0000 IN X 3.0000 IN |
| interrupt rating | 10 kAIC |
| Poles | 4 |
| Trip Type | Common breaker trip |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|--|
| Description | BQC QUAD BRKR 1-30A/2P 1-40A/2P COM. TRIP 120/240V |
| extra long description | ETN BQC230240 BQC Quad 1-30A/2P 1-4 |
| Features | Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF. |
| Long Description | Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (1) Two-Pole 30 A, (1) Two-Pole 40 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC |
| Product Type | BQC Quad 1-30A/2P 1-40A/2P 120/240V 10K |
| Special Features | Includes Rejection Tab feature |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786676371902 |
| Manufacturers Part Number | BQC230240 |
| UPC | 786676371902 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Loadcenter Plug In Breakers and Accessories |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.9 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other |
| standard | UL 489,Federal Specifications Classification W-C375 |