



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BQC2502120 BQC Quad BRKR 1-50A/2P 2-20A/1P Com. Trip 120/240V** *Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | BQC2502120  |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton BR Thermal Magnetic Circuit Breaker, Type BQC 1-Inch CTL Plug-On Circuit Breaker, Includes Rejection Tab Feature, (2) Four-Pole 20 A, (1) Two-Pole 50 A, 10 Kaic, Four-Pole, 120/240V, BQC, Common Breaker Trip, #14-4 Awg Cu/Al, BQC |
| Weight per unit  | 0.9000 (lbs/each)   |
| Product Category | Quadplex Standard Trip Plug-In  |

### Features

|                  |                                   |
|------------------|-----------------------------------|
| dimensions       | 3.0000 IN X 2.0000 IN X 3.0000 IN |
| interrupt rating | 10 kAIC                           |
| Poles            | 4                                 |
| Trip Type        | Common breaker trip               |
| Voltage Rating   | 120/240 V                         |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | BQC QUAD BRKR 1-50A/2P 2-20A/1P COM. TRIP 120/240V   |
| extra long description | ETN BQC2502120 BQC Quad 1-50A/2P 2-  |
| Features               | Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF. |
| Long Description       | Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (2) Four-Pole 20 A, (1) Two-Pole 50 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC  |
| Product Type           | BQC Quad 1-50A/2P 2-20A/1P 120/240V 10K  |
| Special Features       | Includes Rejection Tab feature   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786676371827 |
| Manufacturers Part Number | BQC2502120     |
| UPC                       | 786676371827   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Specialty Breakers (Quad, Dupl, Shunt Trip) |
| Type                 | Thermal magnetic circuit breakers           |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 25  |
| Weight Per each | 0.9 |

## Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | OtherGeneration - Conventional Energy - Conventional<br>EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine<br>Vessels and Equipment - Marine Vessels and Equipment -<br>OtherGeneration - Renewable Energy - Alternative Energy |
| standard    | UL 489,Federal Specifications Classification W-C375   |