



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR1224L400R Singleph Mlo LC 400A 24 CKT Nema 3R *Eaton Corp*

Catalog Number	BR1224L400R
Manufacturer	Eaton Corp
Description	Eaton BR Main Lug Loadcenter, 400 A, 42, Aluminum, Nema 3R, Surface, Nema 3R, 42 Circuits, 24-Pole, 12 Spaces, 3-Wire, Single-Phase, Type BR 1-Inch Breakers, 120/240V, (2) #3/0-400 Kcmil
Weight per unit	48.6 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	400
Cover Type	Cover included
interrupt rating	25
number of spaces	12
Phase	1

Dimensions and Weight

Depth	6.38
Height	38
Width	16.31

Descriptions

Description	SINGLEPH MLO LC 400A 24 CKT NEMA 3R
extra long description	ETN BR1224L400R 1PH MLO LC, 400A, 2
Features	Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets.
Long Description	Eaton BR main lug loadcenter, 400 A,42,Aluminum, NEMA 3R,Surface,NEMA 3R,42 Circuits,24-pole,12 Spaces,3-wire,Single-phase,Type BR 1-inch breakers,120/240V,(2) #3/0-400 kcmil
Product Type	1PH Mlo LC, 400A, 24 CKT, N3R



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786685895420
Manufacturers Part Number	BR1224L400R
UPC	786685895420

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

Packaging

Carton	1
Weight Per each	48.6

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting standard	Surface Mount UL 67,UL 50