

# Specifications



Photo is representative

## Eaton BRP08B150RF

Feed through lugs, Plug-on neutral main circuit breaker loadcenter, 150A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 16 circuits, Single pole, 8 spaces, Three-wire, Single-phase, Feed-through lugs, Combination, NEMA 3R, Type BR 1-inch brea

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main breaker loadcenter
<b>CATALOG NUMBER</b>	BRP08B150RF
<b>UPC</b>	786689059095
<b>PRODUCT LENGTH/DEPTH</b>	25 in
<b>PRODUCT HEIGHT</b>	5.5 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	18 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 67 UL 50



*Powering Business Worldwide*

### Product specifications

**SPECIAL FEATURES**

Feed through lugs

### Resources

<b>TYPE</b>	Plug-on neutral main circuit breaker loadcenter
<b>AMPERAGE RATING</b>	150 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	CSR
<b>NUMBER OF CIRCUITS</b>	16
<b>NUMBER OF POLES</b>	Single-pole
<b>NUMBER OF SPACES</b>	8
<b>PHASE</b>	Single-phase
<b>ACCESSORIES</b>	Feed-through lugs
<b>MOUNTING</b>	Combination
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>BOX SIZE</b>	X4
<b>ENCLOSURE</b>	NEMA 3R
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25 kAIC
<b>NUMBER OF WIRES</b>	3
<b>NEMA RATING</b>	NEMA 3R

**SPECIFICATIONS AND DATASHEETS**

[Eaton Specification Sheet - BRP08B150RF](#)

**WARRANTY GUIDES**

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications



Photo is representative

## Eaton BRP08B150RF

Feed through lugs, Plug-on neutral main circuit breaker loadcenter, 150A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 16 circuits, Single pole, 8 spaces, Three-wire, Single-phase, Feed-through lugs, Combination, NEMA 3R, Type BR 1-inch brea

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main breaker loadcenter
<b>CATALOG NUMBER</b>	BRP08B150RF
<b>UPC</b>	786689059095
<b>PRODUCT LENGTH/DEPTH</b>	25 in
<b>PRODUCT HEIGHT</b>	5.5 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	18 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 67 UL 50



### Product specifications

**SPECIAL FEATURES** Feed through lugs

### Resources

<b>TYPE</b>	Plug-on neutral main circuit breaker loadcenter
<b>AMPERAGE RATING</b>	150 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	CSR
<b>NUMBER OF CIRCUITS</b>	16
<b>NUMBER OF POLES</b>	Single-pole
<b>NUMBER OF SPACES</b>	8
<b>PHASE</b>	Single-phase
<b>ACCESSORIES</b>	Feed-through lugs
<b>MOUNTING</b>	Combination
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>BOX SIZE</b>	X4
<b>ENCLOSURE</b>	NEMA 3R
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25 kAIC
<b>NUMBER OF WIRES</b>	3
<b>NEMA RATING</b>	NEMA 3R

**SPECIFICATIONS AND DATASHEETS**

[Eaton Specification Sheet - BRP08B150RF](#)

**WARRANTY GUIDES**

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

