

# Eaton BRP115AF

Catalog Number: BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR AFCI circuit breaker	BRP115AF
<b>UPC</b>	<b>Product Length/Depth</b>
786689041014	2.56 in
<b>Product Height</b>	<b>Product Width</b>
1.1 in	1 in
<b>Product Weight</b>	<b>Certifications</b>
0.38 lb	UL Listed

**Type**

AFCI Combination circuit breaker

**Special features**

UL only

**Amperage Rating**

15 A

**Voltage rating**

120 V

**Neutral**

Plug-on neutral

**Used with**

Type BR Loadcenters

**Interrupt rating**

10 kAIC

**Main circuit breaker**

BR

**Connection**

Plug-on

**Wire size**

#14-8 AWG Cu/Al

**Number of poles**

Single-pole

**Brochures**

[Loadcenters and Circuit Breakers](#)

**Warranty guides**

[Eaton type BR circuit breaker limited warranty June 2024](#)

# Eaton BRP115AF

Catalog Number: BRP115AF

Eaton BR AFCI circuit breaker, AFCI Combination circuit breaker, UL only, 15 A, 10 kAIC, Single-pole, 120 V, BR, Plug-on, #14-8 AWG Cu/Al, Type BR Loadcenters, Plug-on neutral



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR AFCI circuit breaker	BRP115AF
<b>UPC</b>	<b>Product Length/Depth</b>
786689041014	2.56 in
<b>Product Height</b>	<b>Product Width</b>
1.1 in	1 in
<b>Product Weight</b>	<b>Certifications</b>
0.38 lb	UL Listed

**Type**

AFCI Combination circuit breaker

**Special features**

UL only

**Amperage Rating**

15 A

**Voltage rating**

120 V

**Neutral**

Plug-on neutral

**Used with**

Type BR Loadcenters

**Interrupt rating**

10 kAIC

**Main circuit breaker**

BR

**Connection**

Plug-on

**Wire size**

#14-8 AWG Cu/Al

**Number of poles**

Single-pole

**Brochures**

[Loadcenters and Circuit Breakers](#)

**Warranty guides**

[Eaton type BR circuit breaker limited warranty June 2024](#)