



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-646-6192



## BR215H Type BR 2 Pole 15 Amp 240V

*Eaton Corp*

Catalog Number	BR215H
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On High-Magnetic Circuit Breaker, High-Magnetic, 15 A, 10 Kaic, Two-Pole, 240V, BR, Common Breaker Trip, #14-4 Awg Cu/Al, Q28, BR, Type BR Loadcenters
Weight per unit	0.5000 (lbs/each)
Product Category	2P Special Application Plug-In

### Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10
Poles	Two-pole
Voltage Rating	240 V - 240 V

### Descriptions

Description	TYPE BR 2 POLE 15 AMP 240V
extra long description	ETN BR215H TYPE BR 2 pole 15 amp 24
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on high-magnetic circuit breaker, High-magnetic, 15 A, 10 kAIC, Two-pole, 240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters
Product Type	Type BR 2 Pole 15 Amp 240V
Special Features	High-Magnetic

### Manufacturer Information

Brand	Eaton Corp
Manufacturers Part Number	BR215H

### Taxonomies, Classifications, and Categories

Type	Thermal magnetic circuit breakers
------	-----------------------------------

### Packaging

Carton	1
Weight Per each	0.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-646-6192

## Uses, Certifications, and Standards

Application

OtherGeneration - Renewable Energy - Alternative

EnergyGeneration - Conventional Energy - Conventional

EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine

Vessels and Equipment - Marine Vessels and Equipment - Other

standard

UL 489,Federal Specifications Classification W-C375