



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## BR3060BQN200 30/60C 200A QN MB Loadcenter

*Eaton Corp*

|                  |                                                                                                                                                                                                                     |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | BR3060BQN200                                                                                                                                                                                                        |
| Manufacturer     | Eaton Corp                                                                                                                                                                                                          |
| Description      | BR Style Load Center, 30 Spaces, 60 Circuits, 200 A, 120/240 V Ac, #2 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 34.13 In Overall Height |
| Weight per unit  | 33.0 (lbs/each)                                                                                                                                                                                                     |
| Product Category | Single Phase Main Breaker Load                                                                                                                                                                                      |

### Features

|                      |                                                       |
|----------------------|-------------------------------------------------------|
| amperage rating      | 59120                                                 |
| Box Size             | M104D-731                                             |
| cover                | Cover included                                        |
| Cover Type           | Cover included                                        |
| dimensions           | 98.5520millimetreX36.3474centimetreX86.6902centimetre |
| main circuit breaker | CSR                                                   |
| Number of Wires      | Three-wire                                            |
| Phase                | 1 PH                                                  |
| used with            | Type BR 1-inch breakers                               |

### Material, Color, and Finish

|                    |          |
|--------------------|----------|
| Enclosure Material | Metallic |
|--------------------|----------|

### Dimensions and Weight

|      |           |
|------|-----------|
| Size | M104D-731 |
|------|-----------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 30/60C 200A QN MB LOADCENTER        |
| extra long description | ETN BR3060BQN200 BR style 1-inch lo |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00786676026284 |
| UPC  | 786676026284   |

### Taxonomies, Classifications, and Categories

|                      |                                                                                                                                                                                                                        |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category Description | LOADCENTERS & COVERS                                                                                                                                                                                                   |
| igcc                 | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type                 | Main circuit breaker                                                                                                                                                                                                   |
| unspsc code          | 39121101                                                                                                                                                                                                               |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                       |    |
|-----------------------|----|
| Carton .....          | 1  |
| Weight Per each ..... | 33 |

## Uses, Certifications, and Standards

|                 |             |
|-----------------|-------------|
| Enclosure ..... | NEMA 1      |
| Mounting .....  | Combination |