

Type BR Mechanical Interlock Kits



Type BR Loadcenter with Mechanical Interlock Kit

With the aging electrical infrastructure and frequent severe storms, power outages are becoming more and more frequent affecting thousands of people nationwide. Eaton's Mechanical Interlock kit provides an easy and cost effective solution when using back-up emergency power.

This solution expands the robust line of emergency power products and accessories.

Features & Benefits:

- UL67 Listed – For use with BR loadcenters
- Prevents utility and generator supplies from being on at the same time
- Protects utility linemen from dangerous generator backfeed
- Robust interlock design
- Meets NEC® Article 702
- Offered in two unique styles for almost any BR loadcenter, which can reduce inventory levels
- Quick and easy installation - Drill points or fixtures for pilot holes provided on all applicable BR loadcenters. No additional assembly required



Powering Business Worldwide

Mechanical Interlock Kits and Catalog Numbers



BRMIKCSR



BRMIKBR

Each Mechanical Interlock kit includes:

- Interlock assembly
- Hold Down kit
- New labels
- Necessary screws

Warranty information:

- 10 year warranty on all Type BR circuit breakers and loadcenters
- Refer to Eaton for complete warranty details

Mechanical Interlock Kits

Catalog Number	Description
BRMIKBR*	Single
BRMIKBRBP*	Bulk pack
BRMIKCSR*	Single
BRMIKCSRBP*	Bulk pack

*Clamshell packaged

Loadcenter Catalog Numbers for BRMIKCSR

Indoor	Raintight
BR1630B150	BR816B150RF
BR1224N200	BR816B200RF
BR1632B200	BR816N200RF
BR1632N200	BR1224N200R
BR2030B150	BR2030B150R
BR2030H150	BR2040B150R
BR2040B150	BR2040B200R
BR2040B200,BC200	BR2040B225R
BR2040H200	BR2040N200R
BR2040N200, NC200	BR3030B150R
BR2430B150, BC150	BR3040B200R
BR3030B150	BR3040N200R
BR3030H150	BR4040B200R
BR3040B150	BR4040N200R
BR2440B200	BR4242B225R
BR2440N200	
BR3040B200, BC200	
BR3040N200, NC200	
BR3040H200	
BR4040B200, BC200	
BR4040H200	
BR4040N200, NC200	
BR4242B225	

Loadcenter Catalog Numbers for BRMIKBR

Indoor
BR816B100
BR816N100
BR1212B100
BR1220B100
BR1220H100
BR1224N125
BR1616B100
BR1620B100
BR1624B100
BR1624B125
BR1624N125
BR2020B100, BC100
BR2024H100
BR2020HC100
BR2040B100
BR2024B125
BR2024N125,NC125
BR3030BC100
BR3030HC100
BR2030B100
BR3030B100
BR3030B125
BR3030BC125



Eaton Corporation
 Electrical Sector
 1111 Superior Ave.
 Cleveland, OH 44114
 United States
 877-ETN-CARE (877-386-2273)
 Eaton.com

© 2013 Eaton Corporation
 All Rights Reserved
 Printed in USA
 Publication No. PA003001EN
 October 2013



Proud Sponsor of



For more information or questions, please contact the Lincoln Flex Center at 1-800-330-6479 or email at FlexCenterLincoln@eaton.com.

The National Electrical Code is a registered trademark of the National Fire Protection Association.

All other trademarks are property of their respective owners.