



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRN240GF BR 2 Pole 40A GFST 120/240V 10 Kaic *Eaton Corp*

Catalog Number	BRN240GF
Manufacturer	Eaton Corp
Description	Eaton BR Gfci Circuit Breaker, Ground Fault Personnel Protection Circuit Breakers, Pigtail Neutral, 40 A, 10 Kaic, Two-Pole, 120/240 V, GFTCB, Common, #14-4 Awg, Ground Fault Circuit Interrupter, GFI
Weight per unit	1.0 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	4.2500 IN X 3.0000 IN X 2.0000 IN
------------	-----------------------------------

Descriptions

Description	BR 2 POLE 40A GFST 120/240V 10 KAIC
extra long description	ETN BRN240GF BR 2 POLE 40A GFST, 12
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	EATON BR GFCI CIRCUIT BREAKER, GROUND FAULT PERSONNEL PROTECTION CIRCUIT BREAKERS, PIGTAIL NEUTRAL, 40 A, 10 KAIC, TWO-POLE, 120/240 V, GFTCB, COMMON, #14-4 AWG, GROUND FAULT CIRCUIT INTERRUPTER, GFI
Product Type	BR 2 Pole 40A GFST, 120/240V, 10 Kaic

Manufacturer Information

Brand	Eaton
GTIN	00786676043786
Manufacturers Part Number	BRN240GF
UPC	786676043786

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Datacenters - IT Space: CI and Hyper Converged
Generation - Conventional Energy - Conventional Energy
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other
Other Generation - Renewable Energy - Alternative Energy

standard

UL 489, UL 943