



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BULLET2X12YA (2) 12W Led FLD 30K W/CVR Plate BRZ

Rab Lighting

| | |
|------------------|---|
| Catalog Number | BULLET2X12YA |
| Manufacturer | Rab Lighting |
| Description | Floodlights 2502 Lumens Bullet 24W 3000K Bronze |
| Weight per unit | 4.9 (lbs/each) |
| Product Category | Led Floodlights |

Features

| | |
|-----------------|-------------|
| amperage rating | 0.22A @120V |
| average life | 100000 |
| lumens | 2502 |
| Voltage Rating | 120 |
| Wattage | 24 |

Material, Color, and Finish

| | |
|-----------------------------|------------|
| color rendering index (cri) | 85 CRI |
| color temperature | 3000K Warm |

Dimensions and Weight

| | |
|--------|-----|
| Height | 8 |
| Width | 7.7 |

Descriptions

| | |
|------------------------|--|
| Description | (2) 12W LED FLD 30K W/CVR PLATE BRZ |
| extra long description | RAB BULLET2X12YA BULLETFLD KIT 2X12 |
| Long Description | Floodlights 2502 Lumens Bullet 24W 3000K Bronze |
| Product Type | Bulletfld Kit 2X12W Warm 120V BZ |
| Special Features | Microprismatic diffusion lens optimizes light output without glare |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | RAB Lighting Inc |
| GTIN | 00019813212470 |
| Manufacturers Part Number | BULLET2X12YA |
| UPC | 019813212470 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |
| Type | FLOODLIGHT |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 4.89 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Outdoor Floodlight |
| environmental conditions | Suitable for Wet locations |
| Mounting | Heavy-duty mounting arm with "O" ring seal and stainless steel screws |
| nema rating | NEMA Beam Spread of 6H x 6V |
| standard | Microprismatic diffusion lens optimizes light output without glare |