



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25ANB125H Compact 1P 25A Cont SCR Term Quad QC 277VAC Coil

Eaton Corp

Catalog Number	C25ANB125H
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 25A, 440-480 Vac, 50/60 HZ, Open With Metal Mounting Plate, Compact, Single-Pole, 25A, Contactor, Single-Pole, 35A, Binding Head Screw and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	0.6000 (lbs/each)
Product Category	Definite Purpose Contactors

Features

connection	Quick
dimensions	2.3200 IN X 1.9700 IN X 3.1900 IN
Enclosure Type	Open with metal mounting plate

Dimensions and Weight

Depth	2.32
Height	3.19
Width	1.97

Descriptions

Description	COMPACT 1P 25A CONT SCR TERM QUAD QC 277VAC COIL
extra long description	ETN C25ANB125H COMPCT 1P 25A CONT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 25A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, Compact, single-pole, 25A, Contactor, Single-pole, 35A, Binding head screw and quick connect terminals (side-by-side), Non-reversing
Product Type	Compct 1P 25A Cont SCR TRM 4QC 277vcoil

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685115832
Manufacturers Part Number	C25ANB125H
UPC	786685115832

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	CSA Certified,UL Recognized,RoHS Compliant