



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DNF340H Open N-R 3P 40A DP Cont Box Lugs W/QC Term 277vac

Eaton Corp

Catalog Number	C25DNF340H
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 40A, 12 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 40A, Contactor, Three-Pole, 50A, Box Lugs (Posidrive Setscrew) and Quick Connect Terminals , Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

Enclosure Type	Open with metal mounting plate
----------------	--------------------------------

### Dimensions and Weight

Depth	3.35
Height	3.75
Width	2.4

### Descriptions

Description	OPEN N-R 3P 40A DP CONT BOX LUGS W/QC TERM 277VAC
extra long description	ETN C25DNF340H OP N-R 3P 40ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 40A, 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, Three-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals , Non-reversing
Product Type	Op N-R 3P 40ADPCNT BXLGS W/QC277VCL

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116311682
Manufacturers Part Number	C25DNF340H
UPC	782116311682

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

CSA Certified,UL Recognized,RoHS Compliant