



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BX6 SPRG 4SQ FLX CBL SPRT

Cooper B-Line/Cable Tray

Catalog Number	BX6
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Cable Support Fasteners, Conduit and Cable, 1" Height, 1" Length, 1" Width, 0.08LBS, Flexible Cable Support, 75 LBS Load Capacity, Zinc Plated
Weight per unit	0.0862 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

Cable Type	AC/MC
dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
load	75 Lb
Material	ZINC PLATED STEEL

Descriptions

Description	SPRG 4SQ FLX CBL SPRT
extra long description	B-LINE BX6 FLEXIBLE CBL SPT, 4 SQ "
Features	Eaton B-Line series cable support fasteners are used to support metal clad cables (MC), armored cables (AC), non-metallic cables and flexible conduit in new or retrofit commercial construction.
Long Description	Eaton B-Line series cable support fasteners, Conduit and cable, 1" Height, 1" Length, 1" Width, 0.08lbs, Flexible cable support, 75 lbs load capacity, Zinc plated
Product Type	Flexible CBL SPT, 4 SQ "CH Usable Area
Special Features	Usable Area 4 Sq In

Manufacturer Information

Brand	Eaton
GTIN	00781011197650
UPC	781011197650

Taxonomies, Classifications, and Categories

Category Description	CABLE & PIPE TRANSITS
Type	Cable fastener and support

Packaging

Carton	1
Package	100
Weight Per each	0.0862



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - OtherCommercial /
Institutional Buildings / Structures - Lighting and Lighting
ControlsCommercial / Institutional Buildings / Structures -
Commercial/Inst Bldg Structures - Aftermarket

standard

UL/cUL Listed