



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C29 3/4" Alu C MK9 Conduit Body

*Crouse-Hinds*

Catalog Number	C29
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Mark 9 Conduit Outlet Body, Copper-Free Aluminum, C Shape, 3/4"
Weight per unit	0.4600 (lbs/each)
Product Category	Alum

### Features

dimensions	5.3400 IN X 1.5600 IN X 1.6300 IN
------------	-----------------------------------

### Material, Color, and Finish

Finish	Untreated
--------	-----------

### Dimensions and Weight

Height	1-5/8
Hub Size	3/4 in
Length	5-11/16
Width	1-9/16

### Descriptions

Description	3/4" ALU C MK9 CONDUIT BODY
extra long description	CRS-H C29 3/4 NPT CST AL C MARK 9 C
Features	Mark 9 copper-free aluminum conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide for access to conductors for maintenance and future system changes. Mark 9 bodies are offered in seven different shapes, and they provide more room for heavier conductors.
Long Description	Eaton Crouse-Hinds series Condulet Mark 9 conduit outlet body, Copper-free aluminum, C shape, 3/4"
Product Type	3/4 NPT CST AI C Mark 9 CNDT Body

### Manufacturer Information

Brand	Eaton
GTIN	00782274123004
UPC	782274123004

### Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Conduit outlet body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	5
Weight Per each	0.46

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D