



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C1 #1 Cu Long Barrel Compression Butt Splice

*Nsi Industries*

Catalog Number	C1
Manufacturer	Nsi Industries
Description	Long Barrel TINNEDCOPPERSPLICE1 Awg Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.1000 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Green
Finish	Tin Plated

### Dimensions and Weight

Size	L=2.20 - OD=.469 - ID=.359
------	----------------------------

### Descriptions

Description	#1 CU LONG BARREL COMPRESSION BUTT SPLICE
extra long description	NSI C-1 1 AWG Copper Long Barrel Sp
Features	Long Barrel TinnedCopperSplice1 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	Long Barrel TinnedCopperSplice1 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	1 Awg Copper Long Barrel Splice - Green
Special Features	# 1 AWG (STR) - CU Splice



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381037541
UPC	662381037541

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - CU Splice

## Packaging

Carton	1
Package	50
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)
Temperature Rating	90 C