

# Specifications

## Eaton C37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, C shape, 1"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	C37 SA
<b>UPC</b>	782274123110
<b>PRODUCT LENGTH/DEPTH</b>	7 in
<b>PRODUCT HEIGHT</b>	1.88 in
<b>PRODUCT WIDTH</b>	1.75 in
<b>PRODUCT WEIGHT</b>	0.44 lb



*Powering Business Worldwide*

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

## Product specifications

SHAPE	C
TRADE SIZE	1"
MATERIAL	Copper-free aluminum

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Form 7 catalog page</a>
CERTIFICATION REPORTS	<a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification</a> <a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers UL certification</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 863 - Conduit Body Wire Pulling</a> <a href="#">IF 964 - Conduit Body Wire Pulling</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C37 SA</a> <a href="#">Condulet Form 7 Industrial Grade Conduit Bodies</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Industrial Fittings Bend Radius and Cubic Capacity Chart</a> <a href="#">Industrial Fittings Wire Fill Chart</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.



# Specifications

## Eaton C37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, C shape, 1"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	C37 SA
<b>UPC</b>	782274123110
<b>PRODUCT LENGTH/DEPTH</b>	7 in
<b>PRODUCT HEIGHT</b>	1.88 in
<b>PRODUCT WIDTH</b>	1.75 in
<b>PRODUCT WEIGHT</b>	0.44 lb



*Powering Business Worldwide*

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

## Product specifications

SHAPE	C
TRADE SIZE	1"
MATERIAL	Copper-free aluminum

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Form 7 catalog page</a>
CERTIFICATION REPORTS	<a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification</a> <a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers UL certification</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 863 - Conduit Body Wire Pulling</a> <a href="#">IF 964 - Conduit Body Wire Pulling</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - C37 SA</a> <a href="#">Condulet Form 7 Industrial Grade Conduit Bodies</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Industrial Fittings Bend Radius and Cubic Capacity Chart</a> <a href="#">Industrial Fittings Wire Fill Chart</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

