



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

C4WH6 4-In WHT CVR P/FT *Panduit Corporation*

Catalog Number	C4WH6
Manufacturer	Panduit Corporation
Description	The C4WH6 PVC Flush Wiring Duct Cover Features A Non-Slip, Liner to Prevent Cover Slide. Designed With The User In Mind, The Cover Is Easy to Install and Remove. The General-Purpose Lead-Free PVC Material Is Suitable For Use In Indoor Applications. UI 94 Flame Class Of V-0 With A UI Recognized Continuous-Use Temperature Up to 122°F (50°C). 0.37" X 4.25" (9.4 MM X 108 MM) and 6' (1.83 M) Long. Color White.
Weight per unit	0.0104 (lbs/each)
Product Category	Wiring Duct & Accessories

Features

connection	Snap-on
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Length	6.00
Width	4.25

Descriptions

Description	4-IN WHT CVR P/FT
extra long description	PAN C4WH6 Panduct® C4WH6 Flush Duct
Long Description	The C4WH6 PVC Flush Wiring Duct Cover features a non-slip, liner to prevent cover slide. Designed with the user in mind, the cover is easy to install and remove. The general-purpose lead-free PVC material is suitable for use in indoor applications. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). 0.37" x 4.25" (9.4 mm x 108 mm) and 6' (1.83 m) long. Color White.
Product Type	Panduct® C4WH6 Flush Duct Cover

Manufacturer Information

Brand	PANDUIT
GTIN	00074983231423
Manufacturers Part Number	C4WH6
UPC	074983231423



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description WIRE DUCT AND COVERS

Type Flushed Duct Cover

Availability

minimum qty 6

Packaging

Carton 120

Weight Per foot 0.0104

Uses, Certifications, and Standards

Application Cover for Wiring Duct

standard CE Compliant;CSA Certified;Flammability Ratings: UL94 V-0;RoHS
Compliant;UL Recognized