



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25CNB130T Compact 1P W/Shunt 30A Cont SCR Term Quad QC 24vac *Eaton Corp*

Catalog Number	C25CNB130T
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 30A, 277 Vac, 60 HZ, Open With Metal Mounting Plate, Compact, Single-Pole W/Shunt, 30A, Contactor, Single-Pole, 40A, Binding Head Screw and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	0.6000 (lbs/each)
Product Category	Definite Purpose Contactors

Features

connection	Quick
dimensions	2.3200 IN X 1.9700 IN X 3.1900 IN
Enclosure Type	Open with metal mounting plate

Dimensions and Weight

Depth	2.32
Height	3.19
Width	1.97

Descriptions

Description	COMPACT 1P W/SHUNT 30A CONT SCR TERM QUAD QC 24VAC
extra long description	ETN C25CNB130T CMPCT 1P W/SHNT 30A
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 30A, 277 Vac, 60 Hz, Open with metal mounting plate, Compact, single-pole w/shunt, 30A, Contactor, Single-pole, 40A, Binding head screw and quick connect terminals (side-by-side), Non-reversing
Product Type	CMPCT 1P W/SHNT 30A Cont SCR TRM 4qc24ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685116235
Manufacturers Part Number	C25CNB130T
UPC	786685116235

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	CSA Certified,UL Recognized,RoHS Compliant