



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DNF350T Open N-R 3P 50A DP Cont Box Lugs W/QC Term 24VAC C *Eaton Corp*

Catalog Number	C25DNF350T
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 50A, 24 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Contactor, Three-Pole, 65A, Box Lugs (Posidrive Setscrew) and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	1.3 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

Enclosure Type	Open with metal mounting plate
----------------	--------------------------------

### Dimensions and Weight

Depth	3.35
Height	3.75
Width	2.4

### Descriptions

Description	OPEN N-R 3P 50A DP CONT BOX LUGS W/QC TERM 24VAC C
extra long description	ETN C25DNF350T OP N-R 3P 50ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 50A, 24 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, Contactor, Three-pole, 65A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing
Product Type	Op N-R 3P 50ADPCNT BXLGS W/Qc24ac

### Manufacturer Information

Brand	Eaton
GTIN	00782116311996
Manufacturers Part Number	C25DNF350T
UPC	782116311996

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	1.33



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

UL Recognized, CSA Certified, RoHS Compliant