

# Specifications

## Eaton C27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, C shape, 3/4"



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	C27
<b>UPC</b>	782274122601
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	1.63 in
<b>PRODUCT WIDTH</b>	1.56 in
<b>PRODUCT WEIGHT</b>	1.2 lb

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	12

## Resources

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

**INSTALLATION INSTRUCTIONS** [IF 964 - Conduit Body Wire Pulling](#)  
[IF 863 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Condulet Form 7 Industrial Grade Conduit Bodies](#)  
[Eaton Specification Sheet - C27](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)  
[Industrial Fittings Wire Fill Chart](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Product specifications

<b>SHAPE</b>	C
<b>TRADE SIZE</b>	3/4"
<b>MATERIAL</b>	Feraloy iron alloy



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton C27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, C shape, 3/4"



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	C27
<b>UPC</b>	782274122601
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	1.63 in
<b>PRODUCT WIDTH</b>	1.56 in
<b>PRODUCT WEIGHT</b>	1.2 lb

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	12

## Resources

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)  
[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

**INSTALLATION INSTRUCTIONS** [IF 964 - Conduit Body Wire Pulling](#)  
[IF 863 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Condulet Form 7 Industrial Grade Conduit Bodies](#)  
[Eaton Specification Sheet - C27](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)  
[Industrial Fittings Wire Fill Chart](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

## Product specifications

<b>SHAPE</b>	C
<b>TRADE SIZE</b>	3/4"
<b>MATERIAL</b>	Feraloy iron alloy



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

