

# Specifications

## Eaton CCP2-1-30CC

Eaton Bussmann series CCP UL98 fusible disconnect, 30A, UL98 fusible disconnect, Single-pole, 60 Hz, Class CC, 200



### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series CCP UL98 fusible disconnect
<b>CATALOG NUMBER</b>	CCP2-1-30CC
<b>UPC</b>	051712709163
<b>PRODUCT LENGTH/DEPTH</b>	3.9 in
<b>PRODUCT HEIGHT</b>	3.1 in
<b>PRODUCT WIDTH</b>	0.7 in
<b>PRODUCT WEIGHT</b>	1.46 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL 98

## Electrical rating

AMPERAGE RATING	30A
FREQUENCY RATING	50/60 Hz
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	347 Vac, 125 Vdc

## General information

SPECIAL FEATURES	Finger Safe, 1/4" LOTO
SUITABLE FOR FUSES	LP-CC-1/2 to LP-CC-30 FNQ-R-15 to FNQ-R-20

## Physical details

FUSE TYPE	Class CC
NUMBER OF POLES	Single-pole

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a> <a href="#">CCP2-1-30CC~1 Pole Comp Ckt Protect 30A</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CCP2-1-30CC</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton CCP2-1-30CC

Eaton Bussmann series CCP UL98 fusible disconnect, 30A, UL98 fusible disconnect, Single-pole, 60 Hz, Class CC, 200



### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series CCP UL98 fusible disconnect
<b>CATALOG NUMBER</b>	CCP2-1-30CC
<b>UPC</b>	051712709163
<b>PRODUCT LENGTH/DEPTH</b>	3.9 in
<b>PRODUCT HEIGHT</b>	3.1 in
<b>PRODUCT WIDTH</b>	0.7 in
<b>PRODUCT WEIGHT</b>	1.46 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL 98

## Electrical rating

AMPERAGE RATING	30A
FREQUENCY RATING	50/60 Hz
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	347 Vac, 125 Vdc

## General information

SPECIAL FEATURES	Finger Safe, 1/4" LOTO
SUITABLE FOR FUSES	LP-CC-1/2 to LP-CC-30 FNQ-R-15 to FNQ-R-20

## Physical details

FUSE TYPE	Class CC
NUMBER OF POLES	Single-pole

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a> <a href="#">CCP2-1-30CC~1 Pole Comp Ckt Protect 30A</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CCP2-1-30CC</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

