

Eaton CH12L200R

Catalog Number: CH12L200R

Eaton CH main lug loadcenters, Cover included, Main lug only, 200A, D, Copper, NEMA 3R, Metallic, Overhead, CH, 12, 12, Three-wire, Single-phase, 120/240 V, #4 AWG-300 kcmil



General specifications

Product Name

Eaton CH main lug loadcenter

Catalog Number

CH12L200R

UPC

782113097404

Product Length/Depth

29.13 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

29.8 lb

Warranty

Limited lifetime

Certifications

UL 50

UL 67

Catalog Notes

Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb.

Product specifications

Special features

Cover included

Type

Main lug only

Amperage Rating

200 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

12

Number of spaces

12

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#4 AWG-300 kcmil

Box size

D

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH12L200R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CH12L200R

Catalog Number: CH12L200R

Eaton CH main lug loadcenters,Cover included,Main lug only,200A,D,Copper,NEMA 3R,Metallic,Overhead,CH,12,12,Three-wire,Single-phase,120/240 V,#4 AWG-300 kcmil



General specifications

Product Name

Eaton CH main lug loadcenter

Catalog Number

CH12L200R

UPC

782113097404

Product Length/Depth

29.13 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

29.8 lb

Warranty

Limited lifetime

Certifications

UL 50

UL 67

Catalog Notes

Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb.

Product specifications

Special features

Cover included

Type

Main lug only

Amperage Rating

200 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

12

Number of spaces

12

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#4 AWG-300 kcmil

Box size

D

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH12L200R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)