



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH14B100B

UPC:782113097442

Dimensions:

- **Height:** 3.88 IN
- **Length:** 16.75 IN
- **Width:** 14.31 IN

Notes: Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

Warranties:

- Limited lifetime

Specifications:

- **Type:** Main breaker
- **Amperage Rating:** 100A
- **Box Size:** B
- **Bus Material:** Copper
- **Cover:** Ch8bf-combination, ch8bs-surface, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 14
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #6-1/0 AWG
- **Feed Type:** Top/bottom

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CH MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



Instructions

- [Eaton Specification Sheet - CH14B100B](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH14B100B

UPC:782113097442

Dimensions:

- **Height:** 3.88 IN
- **Length:** 16.75 IN
- **Width:** 14.31 IN

Notes: Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

Warranties:

- Limited lifetime

Specifications:

- **Type:** Main breaker
- **Amperage Rating:** 100A
- **Box Size:** B
- **Bus Material:** Copper
- **Cover:** Ch8bf-combination, ch8bs-surface, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 14
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #6-1/0 AWG
- **Feed Type:** Top/bottom

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CH MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



Instructions

- [Eaton Specification Sheet - CH14B100B](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.