

Specifications



Photo is representative

Eaton CEE56

Eaton Crouse-Hinds series PowerMate CEE back box, 60A, Cast aluminum, 1-1/2", 600 Vac/250 Vdc

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CEE back box |
| CATALOG NUMBER | CEE56 |
| UPC | 662276277045 |
| PRODUCT LENGTH/DEPTH | 4.69 in |
| PRODUCT HEIGHT | 5.69 in |
| PRODUCT WIDTH | 4.25 in |
| PRODUCT WEIGHT | 2.2 lb |



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 60A

| | |
|-----------------------|-----------|
| | Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

| | |
|-----------------------|-----------------|
| TRADE SIZE | 1-1/2" |
| VOLTAGE RATING | 600 Vac/250 Vdc |
| MATERIAL | Cast aluminum |

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CEE56 3D drawing](#)

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - CEE56](#)

[PowerMate Connectors](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton CEE56

Eaton Crouse-Hinds series PowerMate CEE back box, 60A, Cast aluminum, 1-1/2", 600 Vac/250 Vdc

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CEE back box |
| CATALOG NUMBER | CEE56 |
| UPC | 662276277045 |
| PRODUCT LENGTH/DEPTH | 4.69 in |
| PRODUCT HEIGHT | 5.69 in |
| PRODUCT WIDTH | 4.25 in |
| PRODUCT WEIGHT | 2.2 lb |



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 60A

| | |
|-----------------------|-----------|
| | Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

| | |
|-----------------------|-----------------|
| TRADE SIZE | 1-1/2" |
| VOLTAGE RATING | 600 Vac/250 Vdc |
| MATERIAL | Cast aluminum |

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CEE56 3D drawing](#)

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - CEE56](#)

[PowerMate Connectors](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

