



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH240GFT Type BR 5 Ma GFI BRKR 40A/2 Pole 120/240V 10K_Self

Eaton Corp

Catalog Number	CH240GFT
Manufacturer	Eaton Corp
Description	Eaton CH Gfci Circuit Breaker, Ground Fault Circuit Breaker, 40 A, 10 Kaic, Two-Pole, 120/240 V, CH, Common, Plug-On, #14-4 Awg, Ground Fault Self Test, GFI
Weight per unit	0.8000 (lbs/each)
Product Category	In Circuit Breakers

Features

connection	Plug-on
dimensions	4.5000 IN X 2.7500 IN X 2.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR 5 MA GFI BRKR 40A/2 POLE 120/240V 10K_SELF
extra long description	ETN CH240GFT Eaton CH GFCI circuit
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH GFCI circuit breaker,Ground fault circuit breaker,40 A,10 kAIC,Two-pole,120/240 V,CH,Common,Plug-on,#14-4 AWG,Ground fault self test,GFI
Product Type	Eaton CH Gfci Circuit Breaker
Special Features	Ground Fault Self Test

Manufacturer Information

Brand	Eaton
GTIN	00786676025720
Manufacturers Part Number	CH240GFT
UPC	786676025720

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 0.8

Uses, Certifications, and Standards

Application OtherGeneration - Renewable Energy - Alternative
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment -
OtherGeneration - Conventional Energy - Conventional Energy

standard UL 489