



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CF32DTEIN835 32W 4 Pin Triple Tube Biax GX24Q-3 3500K Compact *Sylvania-Ledvance*

Catalog Number	CF32DTEIN835
Manufacturer	Sylvania-Ledvance
Description	Dulux 32W Triple Compact Fluorescent Amalgam Lamp With 4 Pin Base, 3500K Color Temperature, 82 Cri, For Use With Electronic and Dimming Ballasts, Ecologic
Weight per unit	0.2100 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

### Features

amperage rating	Ballast Dependent
average life	16000
Base	GX24q-3
Lamp Type	DULUX T/E
lumens	2,400
Shape	T4X3
start type	ELECTRONIC RAPID START
total harmonic distortion	Ballast Dependent
Voltage	120.00 V
Voltage Rating	Ballast Dependent
Wattage	32

### Material, Color, and Finish

color temperature	3500
Finish	Phosphor Coated

### Dimensions and Weight

Length	5.6
--------	-----

### Descriptions

Description	32W 4 PIN TRIPLE TUBE BIAx GX24Q-3 3500K COMPACT
extra long description	SYL CF32DT/E/IN/835/ECO/20885 CF32D
Long Description	DULUX 32W triple compact fluorescent amalgam lamp with 4 pin base, 3500K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC
Product Type	CF32DTEIN835ECO 50/CS 1/Sku

### Manufacturer Information

Brand	OSRAM SYLVANIA
GTIN	00046135208850
Manufacturers Part Number	CF32DT/E/IN/835/ECO/20885
UPC	046135208850



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... Compact Fluorescent

## Packaging

Carton ..... 1

Package ..... 50

Weight Per each ..... 0.21

## Uses, Certifications, and Standards

Application ..... Commercial/Residential