



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHEC42N225LRNSP CH Surge Ready Loadcctr 42 CKT 225A Convertible MR

Eaton Corp

Catalog Number	CHEC42N225LRNSP
Manufacturer	Eaton Corp
Description	Eaton CH Surge Loadcenter, Includes Renovation Terminal Blocks, Type CH Surge Ready Loadcenter, 225 A, 42 Circuits
Weight per unit	24.0 (lbs/each)
Product Category	Single Phase Convertible Load

### Features

amperage rating	225
interrupt rating	25
media	Yes
number of spaces	42
Phase	1

### Dimensions and Weight

Depth	39.5
Height	4.25
Width	15

### Descriptions

Description	CH SURGE READY LOADCNR 42 CKT 225A CONVERTIBLE MR
extra long description	ETN CHEC42N225LRNSP CH Sur Rdy LC,4
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH surge loadcenter,Includes renovation terminal blocks,Type CH surge ready loadcenter,225 A,42 Circuits
Product Type	CH Sur Rdy LC, 42 CKT, 225A, Conv, MR. SP
Special Features	Includes renovation terminal blocks

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116984176
Manufacturers Part Number	CHEC42N225LRNSP
UPC	782116984176



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... LOADCENTERS & COVERS

Type ..... Surge loadcenter

## Packaging

Carton ..... 1

Weight Per each ..... 24

## Uses, Certifications, and Standards

Application ..... Elec Assemblies, Panels & OEM - Electrical Assemblies and  
EOEMs - Other

standard ..... UL Listed