



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH140 1P 40A 120V Breaker

Eaton Corp

Catalog Number	CH140
Manufacturer	Eaton Corp
Description	Eaton BR140 Eaton HQP1040 Geindust GTHQL1140 Geindust THQL1140 Geindust THQP140 Grainger 1D243 Grainger 1D345 Ite TL412C Schneider HOM140 Schneider QO140 Siemens D140 Siemens TL412R1 Squared HOM140 Squared Qo140
Weight per unit	0.2000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

amp	40
amps	40
dimensions	3.5000 IN X 3.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
main circuit breaker	CH
pole	1
pole #	Single
Poles	1
used with	Type CH Loadcenters
Voltage Rating	120/240 V
Wire Size	#14-2 AWG Cu/Al

Dimensions and Weight

Height	3
Length	3.5
Width	3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	1P 40A 120V BREAKER
extra long description	ETN CH140 CH14096-4604-9
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton BR140 Eaton HQP1040 GEIndust GTHQL1140 GEIndust THQL1140 GEIndust THQP140 Grainger 1D243 Grainger 1D345 ITE TL412C Schneider HOM140 Schneider QO140 Siemens D140 Siemens TL412R1 SquareD HOM140 SquareD QO140
Product Type	CH14096-4604-9

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113101675
Manufacturers Part Number	CH140
UPC	782113101675

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyOtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489