



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH24L3225D 3PH/CH Loadctr 225A Mlo 24 Cir. Cu Bus Nema 1

Eaton Corp

Catalog Number	CH24L3225D
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenter, Standard, Main Lug Only, 225 A, D, Copper, Nema 1, Metallic, Top/Bottom, CH, 24 Circuits, 24 Spaces, Four-Wire, Three-Phase, #4 Awg-300 Kcmil
Weight per unit	18.7 (lbs/each)
Product Category	Three Phase Main Lug Load Cent

Features

amperage rating	225
interrupt rating	35
media	Yes
number of spaces	24
Phase	3

Dimensions and Weight

Depth	29.13
Height	3.88
Size	D
Width	14.31

Descriptions

Description	3PH/CH LOADCNTR 225A MLO 24 CIR. CU BUS NEMA 1
extra long description	ETN CH24L3225D 3Ph/CH LC 225A MLO 2
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenter,Standard,Main lug only,225 A,D,Copper,NEMA 1,Metallic,Top/bottom,CH,24 Circuits,24 Spaces,Four-wire,Three-phase,#4 AWG-300 kcmil
Product Type	3PH/CH LC 225A Mlo 24 CKT Cu Bus Nema 1
Special Features	Standard

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113097671
Manufacturers Part Number	CH24L3225D
UPC	782113097671



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LOADCENTERS & COVERS

Type Main lug loadcenter

Packaging

Carton 1

Weight Per each 18.7

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard UL 67,UL 50