

Eaton CHFN120AF

Catalog Number: CHFN120AF

Eaton CH AFCI circuit breaker, CH Combo AFCI Breaker, 20A, Pigtail, 10 kAICkAIC, 20A, 10 kAIC , CH Combo AFCI Breaker, 20A, Pigtail, 10 kAICkAIC

General specifications



Product Name

Eaton CH AFCI circuit breaker

Catalog Number

CHFN120AF

UPC

786689058845

Product Length/Depth

4.5 in

Product Height

3.25 in

Product Width

0.75 in

Product Weight

0.5 lb

Certifications

UL Listed

Photo is representative

Type

AFCI circuit breakers

Application

CH Combo AFCI Breaker, 20A, Pigtail, 10kAIC

Amperage Rating

20 A

Circuit breaker type

CH

Interrupt rating

10 kAIC

Connection

Pigtail

Number of poles

Single-pole

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - CHFN120AF

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton CHFN120AF

Catalog Number: CHFN120AF

Eaton CH AFCI circuit breaker, CH Combo AFCI Breaker, 20A, Pigtail, 10 kAICkAIC, 20A, 10 kAIC , CH Combo AFCI Breaker, 20A, Pigtail, 10 kAICkAIC

General specifications



Product Name

Eaton CH AFCI circuit breaker

Catalog Number

CHFN120AF

UPC

786689058845

Product Length/Depth

4.5 in

Product Height

3.25 in

Product Width

0.75 in

Product Weight

0.5 lb

Certifications

UL Listed

Photo is representative

Type

AFCI circuit breakers

Application

CH Combo AFCI Breaker, 20A, Pigtail, 10kAIC

Amperage Rating

20 A

Circuit breaker type

CH

Interrupt rating

10 kAIC

Connection

Pigtail

Number of poles

Single-pole

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - CHFN120AF

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia