

Eaton CHFEP120

Catalog Number: CHFEP120

Eaton CH GFCI circuit breaker, Ground fault equipment protector, Trip flag, 20 A, 10 kAIC, Single-pole, 120/240 V, CHFEP, Ground fault circuit interrupter, GFI, 30 mA



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH GFCI circuit breaker	CHFEP120
UPC	Product Length/Depth
786685627977	7.25 in
Product Height	Product Width
6.5 in	6.75 in
Product Weight	Warranty
3.33 lb	Limited lifetime
Certifications	Catalog Notes
UL 489	Switching Duty Rated, HACR Rated

Product specifications

Type

Ground fault equipment protector

Special features

Trip flag

Amperage Rating

20 A

Voltage rating

120/240 V

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Protection

30 mA

Interrupt rating

10 kAIC

Main circuit breaker

CHFEP

Number of poles

Single-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHFEP120](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHFEP120

Catalog Number: CHFEP120

Eaton CH GFCI circuit breaker, Ground fault equipment protector, Trip flag, 20 A, 10 kAIC, Single-pole, 120/240 V, CHFEP, Ground fault circuit interrupter, GFI, 30 mA



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH GFCI circuit breaker	CHFEP120
UPC	Product Length/Depth
786685627977	7.25 in
Product Height	Product Width
6.5 in	6.75 in
Product Weight	Warranty
3.33 lb	Limited lifetime
Certifications	Catalog Notes
UL 489	Switching Duty Rated, HACR Rated

Product specifications

Type

Ground fault equipment protector

Special features

Trip flag

Amperage Rating

20 A

Voltage rating

120/240 V

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Protection

30 mA

Interrupt rating

10 kAIC

Main circuit breaker

CHFEP

Number of poles

Single-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHFEP120](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)