



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHT1520 Type CHT Twin BRKR 1-15/1P 1-20/1P 120/240V 10K *Eaton Corp*

Catalog Number	CHT1520
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CHT Twin Breaker, 15-20 A, 10 Kaic, Single-Pole, 120/240V, CHT, #14-8 Awg Cu/Al, CHT, Type CH Loadcenters, 50-60 HZ, Switching Duty Rated, Hcar Rated
Weight per unit	0.2800 (lbs/each)
Product Category	1P Special Application Plug-In

Features

dimensions	0.7000 IN X 0.5000 IN X 2.6000 IN
interrupt rating	10 kAIC
Poles	1
Voltage Rating	120/240 V

Descriptions

Also Known As...	Piggyback Breaker Peanut Mini-Breaker Half (1/2) Size Breaker Cheater: Breaker Twin Breaker
Description	TYPE CHT TWIN BRKR 1-15/1P 1-20/1P 120/240V 10K
extra long description	ETN CHT1520 CHT TWIN 1-15/1P 1-20/1
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CHT twin breaker, 15-20 A, 10 kAIC, Single-pole, 120/240V, CHT, #14-8 AWG Cu/Al, CHT, Type CH Loadcenters, 50-60 Hz, Switching duty rated, HCAR rated
Product Type	CHT Twin 1-15/1P 1-20/1P 120/240V 10K



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113631554
Manufacturers Part Number	CHT1520
UPC	782113631554

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.28

Uses, Certifications, and Standards

Application	Marine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: Cl and Hyper Converged
Frequency Rating	50-60 Hz
standard	UL Listed,UL 489