



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHU4N9NS Unmetered 30/20 WRTR

Eaton Corp

Catalog Number	CHU4N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Water and Tamper Resistant Center Receptacle, Unmetered, 30A, 20A, None, Non-Ground Fault, Non-Ground Fault, None, Top, Surface, Circuits: 4, Nema TT-30R, Nema 5-20R2GFI (3), None, 3, 3, 0, 125V, 125V, None
Weight per unit	15.0 (lbs/each)
Product Category	20191211090026

### Features

dimensions	18.2500 IN X 10.2500 IN X 8.0000 IN
Mounting Type	Surface

### Dimensions and Weight

Height	8
Length	18.25
Width	10.25

### Descriptions

Description	UNMETERED 30/20 WRTR
extra long description	ETN CHU4N9NS UNMETERED, 30/20, WRTR
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Water and tamper resistant center receptacle, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI (3), None, 3, 3, 0, 125V, 125V, None
Product Type	Unmetered, 30/20, WRTR
Special Features	Water and tamper resistant center receptacle

### Manufacturer Information

Brand	Eaton
GTIN	00786685406350
Manufacturers Part Number	CHU4N9NS
UPC	786685406350

### Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	15

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588