



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CL225 Type CL BRKR 25A/2POLE 120/240V 10K-Classified CKT

*Eaton Corp*

Catalog Number	CL225
Manufacturer	Eaton Corp
Description	Eaton Classified 1" Thermal Magnetic Circuit Breaker, Type CL 1-Inch Classified Replacement Breaker, 25 A, 10 Kaic, Two-Pole, 120/240V, CL, Common Breaker Trip, #14-4 Awg Cu/Al, CL, Type CH Loadcenters
Weight per unit	0.5000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

### Features

dimensions	1.9000 IN X 2.0000 IN X 2.5000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

### Descriptions

Description	TYPE CL BRKR 25A/2POLE 120/240V 10K-CLASSIFIED CKT
extra long description	ETN CL225 CL 25A/2Pole 120/240V 10K
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	Eaton Classified 1" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 25 A, 10 kAIC, two-pole, 120/240V, CL, common breaker trip, #14-4 AWG Cu/Al, CL, Type CH loadcenters
Product Type	CL 25A/2POLE 120/240V 10K

### Manufacturer Information

Brand	Eaton
GTIN	00786676011648
Manufacturers Part Number	CL225
UPC	786676011648

### Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	1" Thermal magnetic circuit breakers

### Packaging

Carton	1
Package	5
Weight Per each	0.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional  
EnergyGeneration - Renewable Energy - Alternative  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherOther

standard

UL 489