



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR7N7N5NS Metered Ringless Surf Pop (2) 5-20R2GFI (1) 6-

Eaton Corp

Catalog Number	CHR7N7N5NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: Non-GND Fault, Pos 2: Non-GND Fault, Pos 3: Non-GND Fault, Top, Surface, Circuits: 4, Center: Nema 5-20R2GFI, Left: Nema 5-20R2GFI, Right: Nema 6-20R2, Ringless
Weight per unit	24.0 (lbs/each)
Product Category	Metered Power Outlet Panels

Features

dimensions	31.0000 IN X 10.0000 IN X 8.0000 IN
------------	-------------------------------------

Dimensions and Weight

Depth	31
Height	8
Width	10

Descriptions

Description	METERED RINGLESS SURF POP (2) 5-20R2GFI (1) 6-
extra long description	ETN CHR7N7N5NS MTRD RL SURF POP(2)5
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Top, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 5-20R2GFI, Right: NEMA 6-20R2, Ringless
Product Type	MTRD RL Surf Pop(2)520R2GFI(1)620R2 Rec

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114203460
Manufacturers Part Number	CHR7N7N5NS
UPC	782114203460

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL Listed file E163588,UL 231