

# Eaton CMBE4242B200BTS

Catalog Number: CMBE4242B200BTS

Eaton Meter Breaker EUSERC ,Type CH EUCERC ,CSR2200N main breaker,Distribution section,200A, 120/240V, Ring, 42 spaces, 42 circuits, 22 kAIC,Surface mounting, Box size D, Al bus, OH/UG feed, 4-jaws, #6-250 kcmil line, #6-250 kcmil ground

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton meter breaker EUSERC	CMBE4242B200BTS
<b>UPC</b>	<b>Product Length/Depth</b>
782114869222	5.38 in
<b>Product Height</b>	<b>Product Width</b>
34.38 in	22 in
<b>Product Weight</b>	<b>Warranty</b>
68 lb	Limited lifetime
<b>Compliances</b>	<b>Certifications</b>
EUSERC Approved	UL Listed

## defaultTaxonomyAttributeLabel

### Special features

Distribution section

### Type

All-in-ones

### Utility approvals

AZ : Arizona Public Service Company

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

AZ : Salt River Project (SRP)

CA : PacifiCorp/Pacific Power/Rocky Mountain Power

ID : PacifiCorp/Pacific Power/Rocky Mountain Power

OR : PacifiCorp/Pacific Power/Rocky Mountain Power

UT : PacifiCorp/Pacific Power/Rocky Mountain Power

WA : PacifiCorp/Pacific Power/Rocky Mountain Power

WY : PacifiCorp/Pacific Power/Rocky Mountain Power

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

AZ : Tucson Electric Power/ UniSource

AZ : Sulphur Springs Valley Electric Coop

WA : Puget Sound Energy

WA : Tacoma Public Utilities

### Interrupt rating

10 kAIC

### Box size

D

### Enclosure

NEMA 3R

### Ground

#6-250 kcmil

### Voltage rating

120/240 V

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER BREAKER PHOENIX STYLE

### Specifications and datasheets

Technical Data Residential Meter Breakers: Type CH and BR Residential

Eaton Specification Sheet - CMBE4242B200BTS

Number of sockets

1

Phase

Single-phase

Used with

Type CH breakers

Number of circuits

42

Bus material

Copper

Feed type

Top/bottom

Main circuit breaker

CSR2200N

Number of jaws

Four-jaw



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)