



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR8N8NSU Pop, Ringless, (2) 5-20R2GFI Receptacles, BTM Feed

Eaton Corp

Catalog Number	CHR8N8NSU
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: GND Fault, Pos 2: Non-GND Fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-Resist Center and Left Receptacle, Center: Nema 5-20R2GFI WR, Left: Nema 5-20R2GFI WR, Right: None, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

Features

Mounting Type	Surface
---------------	---------

Dimensions and Weight

Height	31
Length	7.25
Width	10

Descriptions

Description	POP, RINGLESS, (2) 5-20R2GFI RECEPTACLES, BTM FEED
extra long description	ETN CHR8N8NSU POP RINGLS (2) 5-20R2G
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: None, Ringless
Product Type	Pop RINGLS (2) 5-20R2GFI Recps BTM Feed
Special Features	Water resistant left/center receptacle

Manufacturer Information

Brand	Eaton
GTIN	00786685404202
Manufacturers Part Number	CHR8N8NSU
UPC	786685404202

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 30

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard UL Listed file E163588,UL 231