



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CL390 Ac/DC Digital Clamp Meter, Auto-Ranging 400 Amp

Klein Tools

| | |
|------------------|---|
| Catalog Number | CL390 |
| Manufacturer | Klein Tools |
| Description | Klein Tools CL390 Is An Automatically Ranging True Root Mean Squared (TRMS) Digital Clamp Meter. It Measures Ac/DC Current and NCVT Via The Clamp, Ac/DC Voltage, DC Microamps, Resistance, Continuity, Frequency, Capacitance, and Diodes Via Test Leads, and Temperature Via A Thermocouple Probe. It Features A High Visibility, Reverse Contrast LCD Display That Optimizes View Ability Both In Dark or Bright Ambient Lighting. |
| Weight per unit | 0.5160 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|-------------------|--|
| ac voltage | 600 V |
| auto-power off | Yes |
| Capacitance | 4000 μ F |
| display | 4000 Count Reverse Contrast LCD |
| functions | TRMS, AC/DC Current, NCVT, AC/DC Voltage, Resistance, DC microamp, Frequency, Capacitance, Continuity, Duty Cycle, Diode Test, and Temperature |
| included | Clamp Meter; Carrying Case; Instructions; Test Leads; Thermocouple; Batteries |
| Material | ABS/Electronics |
| media | Yes |
| Overall Height | 1.5" (3.8 cm) |
| Overall Width | 3.5" (8.9 cm) |
| Temperature Range | -40° - 1832°F (-40° - 1000°C) |
| Voltage | 600 V AC/DC |

Dimensions and Weight

| | |
|----------------|-----------------|
| Overall Length | 8.45" (21.5 cm) |
|----------------|-----------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | AC/DC DIGITAL CLAMP METER, AUTO-RANGING 400 AMP |
| extra long description | KLEIN CL390 AC/DC Digital Clamp Met |
| Features | Klein Tools CL390 is an automatically ranging true root mean squared (TRMS) digital clamp meter. It measures AC/DC current and NCVT via the clamp, AC/DC voltage, DC microamps, resistance, continuity, frequency, capacitance, and diodes via test leads, and temperature via a thermocouple probe. It features a high visibility, reverse contrast LCD display that optimizes view ability both in dark or bright ambient lighting. |
| Long Description | Klein Tools CL390 is an automatically ranging true root mean squared (TRMS) digital clamp meter. It measures AC/DC current and NCVT via the clamp, AC/DC voltage, DC microamps, resistance, continuity, frequency, capacitance, and diodes via test leads, and temperature via a thermocouple probe. It features a high visibility, reverse contrast LCD display that optimizes view ability both in dark or bright ambient lighting. |
| Product Type | Ac/DC Digital Clamp Meter |
| Special Features | Automatically Ranging True Root Mean Squared (TRMS) Measurement Technology for Accuracy; AC/DC Current Measurement; High Visibility Reverse Contrast LCD; NCVT |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Klein Tools |
| GTIN | 00092644692871 |
| Manufacturers Part Number | CL390 |
| UPC | 092644692871 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
| Type | AC/DC Current TRMS Clamp |

Packaging

| | |
|-----------------|---------------|
| Carton | 1 |
| Weight | 11 oz (314 g) |
| Weight Per each | 0.516 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Measures both AC/DC current and NCVT via the clamp and AC/DC voltage, DC microamp current, resistance, continuity, frequency, duty-cycle, capacitance and tests diodes via the test leads, and temperature with thermocouple |
| standard | CATIII 600V, Class 2, Double Insulation Safety Rating, CE Certified |