



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CPX2X4AL08SWW7M2 2X4 Led Flat Panel Kelvin/Lumen Select 35K/4K/5K *Lithonia Lighting*

Catalog Number	CPX2X4AL08SWW7M2
Manufacturer	Lithonia Lighting
Description	The 2 FT. X 4 FT. CPX Panel From Lithonia Lighting Is The Perfect Choice For A Quality Led Panel At An Affordable Price. The Smooth, Even Lens Projects A Crisp and Clean Aesthetic. This CPX Configuration Offers Adjustable Light Output (Alo) For The Option Of 3800-6200 Lumens and Switchable White (SWW) For Three Color Temperature In One - 35/40/50K CCT. CPX Is The Perfect Choice For Budget-Conscious School, Commercial Office, or Small Retail Footprint Projects.
Weight per unit	13.5 (lbs/each)
Product Category	Lighting

Features

average life	60
connection	Hardwired
dimensions	47.875 x 23.875 x 1.68
Fixture Type	Flat Panel
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	4000 ,5000 ,6000 ,Switchable
Material	Steel
media	Yes
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	5
Wattage	51

Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	3500 ,4000 ,5000 ,Variable
Finish	Semi-Gloss
Lens Color	WHITE
Style	Traditional



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Height	1.7
Length	47.8
Size	47.875x23.875x1.68
Width	23.8

Descriptions

Construction	New Construction,Remodel
Description	2X4 LED FLAT PANEL KELVIN/LUMEN SELECT 35K/4K/5K
extra long description	LITH CPX 2X4 ALO8 SWW7 M2 LED Flat
Features	Contractor Select
Long Description	The 2 ft. x 4 ft. CPX panel from Lithonia Lighting is the perfect choice for a quality LED panel at an affordable price. The smooth, even lens projects a crisp and clean aesthetic. This CPX configuration offers Adjustable Light Output (ALO) for the option of 3800-6200 lumens and Switchable White (SWW) for three color temperature in one - 35/40/50K CCT. CPX is the perfect choice for budget-conscious school, commercial office, or small retail footprint projects.
Product Type	Flat Panel

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193048542844
Manufacturers Part Number	CPX 2X4 ALO8 SWW7 M2
UPC	193048542844

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Flat Panel

Trade Size

aperture size	2x4
---------------	-----

Packaging

Carton	1
Package	2
Weight Per each	13.5

Uses, Certifications, and Standards

Application	Education,Government,Hospitality,House of Worship,Offices & Banks,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed,Surface,Suspended
standard	CSADLC Premium,DLC Standard