

# Eaton CMB1212B200BTS

Catalog Number: CMB1212B200BTS

Eaton resi meter breaker, All-in-ones, 200 A, C, Copper, NEMA 3R, Bottom and top, #6-350 kcm10 kAIC, #6-350 kcmCSR2200, Surface mounting, 12, Four-jaw, 1, 12, Single-phase, Ringless, Type CH breakers, 120/240 Vac

## General specifications

Product Name	Catalog Number
Eaton residential meter breaker	CMB1212B200BTS
UPC	Product Length/Depth
782114858561	5.38 in
Product Height	Product Width
32.38 in	14.44 in
Product Weight	Warranty
42 lb	Limited lifetime
Certifications	
UL Listed	



## Product specifications

### Special features

With feed through lugs

### Interrupt rating

10 kAIC

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

### Phase

Single-phase

### Ground

#6-350 kcmil

### Bus material

Copper

### Number of jaws

Four-jaw

### Main circuit breaker

CSR2200

### Enclosure

NEMA 3R

### Type

All-in-ones

### Feed type

Top/bottom

### Number of sockets

1

### Used with

Type CH breakers

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Drawings

[Dimensional Drawing - METER BREAKER EAST COAST STYLE](#)

### Specifications and datasheets

[Technical Data Residential Meter Breakers: Type CH and BR Residential](#)

[Eaton Specification Sheet - CMB1212B200BTS](#)

Voltage rating

120/240 V

Number of circuits

12

Box size

C



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)