

# Specifications

## Eaton CRC6044BC

Eaton Crouse-Hinds series PowerMate CRC connector, 60A, 0.440-1.375", Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CRC connector
<b>CATALOG NUMBER</b>	CRC6044BC
<b>UPC</b>	662276276574
<b>PRODUCT LENGTH/DEPTH</b>	8.3 in
<b>PRODUCT HEIGHT</b>	2.31 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	2.2 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**AMPERAGE RATING** 60A

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

<b>GROUNDING TYPE</b>	Style 1
<b>CONFIGURATION</b>	Four-wire, four-pole
<b>CABLE DIAMETER</b>	0.440-1.375"
<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds CRC6044BC 3D drawing](#)

**BROCHURES** [PowerMate Drilling Pin and Sleeve Devices brochure](#)

**CATALOGS** [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

**CERTIFICATION REPORTS** [PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

**INSTALLATION INSTRUCTIONS** [IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - CRC6044BC](#)

[PowerMate Connectors](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

