



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **CNYLEDAL0SWW2UV0 34/52/75W Led Canopy 3K/4K/5K 5000-1000LM** *Lithonia Lighting - Acuity*

Catalog Number	CNYLEDAL0SWW2UV0
Manufacturer	Lithonia Lighting - Acuity
Description	The Cny Led Alo Canopy Luminaire From Lithonia Lighting Is Where Versatility Meets Innovation! With An Incredible 54 Customizable Options Packed Into A Single Luminaire, You Have The Power To Tailor Your Lighting Experience Right On The Spot. Adjust Color Temperature, Lumen Output, Photocell Settings, and Even Activate The Integrated Motion Sensor. It'S Your Lighting, Your Way! The Cny Led Alo'S 10" X 10" Footprint, Matching That Of Typical Hid Luminaires, Goes Beyond Aesthetics. It Expertly Conceals Any U
Weight per unit	5.2 (lbs/each)
Product Category	Lighting

### **Features**

average life	50,000
dimmable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	10,000 LM,5000 LM,5500 LM,6500 LM,7500 LM,8500 LM
Material	Aluminum
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Square
Voltage Rating	120-347
Warranty	5
Wattage	75

### **Material, Color, and Finish**

Color	Bronze
color rendering index (cri)	80
color temperature	Variable
Finish	Gloss
Lens Color	Clear
Lens Material	Polycarbonate
Style	Traditional



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Dimensions and Weight

Height	3
Length	10
Width	10

## Descriptions

Description	34/52/75W LED CANOPY 3K/4K/5K 5000-1000LM
extra long description	LITH CNY LED ALO SWW2 UVOLT PE PIR
Features	Contractor Select
Long Description	The CNY LED ALO Canopy Luminaire from Lithonia Lighting is where versatility meets innovation! With an incredible 54 customizable options packed into a single luminaire, you have the power to tailor your lighting experience right on the spot. Adjust color temperature, lumen output, photocell settings, and even activate the integrated motion sensor. It's your lighting, your way! The CNY LED ALO's 10" x 10" footprint, matching that of typical HID luminaires, goes beyond aesthetics. It expertly conceals any u
Product Type	Canopy

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00197589495041
Manufacturers Part Number	CNY LED ALO SWW2 UVOLT PE PIR
UPC	197589495041

## Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

## Trade Size

aperture size	10 IN
---------------	-------

## Packaging

Carton	1
Package	2
Weight Per each	5.15

## Uses, Certifications, and Standards

Application	Offices & Banks,Retail
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	C-UL-USCA Title 24,DLC Premium