



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CNYLEDP150KMVOLT 47W Led Cnpy 50K 4500LM BRZ

Lithonia Lighting

Catalog Number	CNYLEDP150KMVOLT
Manufacturer	Lithonia Lighting
Description	The Cny Led Canopy Luminaires Are Energy Efficient and Budget Friendly, Perfect For Replacing Up to 400W Metal Halide Luminaires While Saving Up to 80% Energy Costs. Quick Mount Mechanism Significantly Reduces The Installation Time. An Led Array and Translucent Lens Create Uniform and Visually Comfortable Illumination. Cny Led Luminaires Are DLC Premium Listed and Deliver Quick Payback!
Weight per unit	6.0 (lbs/each)
Product Category	20190225083116

Features

average life	50,000
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
media	Yes
pallet quantity	96
Shape	Square
Voltage Rating	120-277
Warranty	5
Wattage	35

Material, Color, and Finish

Color	Bronze
color rendering index (cri)	70
Finish	Gloss
Style	Traditional

Dimensions and Weight

Height	4.125
Length	10.25
Width	10.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	47W LED CNPY 50K 4500LM BRZ
extra long description	LITH CNY LED P1 50K MVOLT DDB M4 CN
Long Description	The CNY LED canopy luminaires are energy efficient and budget friendly, perfect for replacing up to 400W metal halide luminaires while saving up to 80% energy costs. Quick mount mechanism significantly reduces the installation time. An LED array and translucent lens create uniform and visually comfortable illumination. CNY LED luminaires are DLC Premium listed and deliver quick payback!
Product Type	Canopy

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848093337
Manufacturers Part Number	CNY LED P1 50K MVOLT DDB M4
UPC	191848093337

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
Type	Canopy

Packaging

Carton	1
Weight	6.5
Weight Per each	6

Uses, Certifications, and Standards

Application	Offices & Banks,Retail
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	C-UL-USDLC Premium