ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
21330 Inverness Forest Blvd
77073-0000, TX Houston
Phone: 832-626-1994
Fax: 832-626-1995



CSB120LA Switch Toggle SP 20A 120/277V B/Swire La

Eaton Wiring Devices

Catalog Number	CSB120LA
Manufacturer	Eaton Wiring Devices
Description	Eaton Commercial Grade Toggle Switch, #14-10 Awg, 20A, Flush, 120/277V, Back and Side, Screw, Light Almond, Load Type: Motor Control, Fan, Led, Incandescent, Elv, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC
Weight per unit	0.2000 (lbs/each)
Product Category	Miniature/Appliance WRG Dev

Features

amperage rating	20
dimensions	1.3000 IN X 0.9020 IN X 4.2000 IN
Material	PVC
Poles	Single-pole
Voltage Rating	120/277 V

Descriptions

Description	SWITCH TOGGLE SP 20A 120/277V B/SWIRE LA
extra long description	EWD CSB120LA Switch Toggle SP 20A 1
Features	Eaton's Arrow Hart commercial specification grade switches are designed to provide superior quality, reliability and performance in a variety of commercial environments.
Long Description	Eaton commercial grade toggle switch, #14-10 AWG, 20A, Flush, 120/277V, Back and side, Screw, Light almond, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Single-Pole, Brass, PVC
Product Type	Switch Toggle SP 20A 120/277V B/Swire La
Special Features	Commercial Grade

Manufacturer Information

Brand	Eaton
GTIN	00032664719042
Manufacturers Part Number	CSB120LA
UPC	032664719042

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Commercial grade toggle switch

Packaging

Carton	1
Package	50
Weight Per each	0.2

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
21330 Inverness Forest Blvd
77073-0000, TX Houston
Phone: 832-626-1994
Fax: 832-626-1995

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	NOM,Federal Specification Classification 6241 05,cULus Listed